

EdgeConnect™ Twist-Lock®,
Industrial, Flanged Inlet, 30A 250V,
2-Pole 3-Wire Grounding

By Hubbell Wiring Device-Kellems
Catalog # [HBL2625ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Industrial,
Flanged Inlet, 30A 250V, 2-Pole 3-Wire Grounding, L6-30P,
Screwless Terminal, White

Features

- Faster termination time
- No need for torque wrench
- Strong steel spring eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

General

Catalog Number	HBL2625ST
Item Type	Flanged Inlet
Number Of Poles	2
Series	EdgeConnect™
UPC	783585719030

Electrical Ratings

Current / Amperage Rating	30 A
Voltage Rating	250 V

Conductor Related

Number Of Wires	3
-----------------	---

Logistics



Carton Quantity 40

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - EdgeConnect Brochure](#)
- [Catalog Page - WDK B-28 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2976](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EP_WDK_MFG_00069-CANFR-102022](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - EP_WDK_MFG_00069-CANEN-sept2022](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M14338](#)
- [Specifications - HBL2625ST Specification Sheet French](#)
- [Specifications - WIRING_HBL2625ST_spec](#)
- [Specifications - HBL2625ST Specification Sheet English](#)
- [Video - Twist-Lock® Edge Plugs and Inlets](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)