



Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2641](#)



Twist-Lock® Male Plug 30A, 480V, 2-Pole, 3-Wire Grounding, L8-30P/White.

Features

- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

Application

Extra Heavy Duty Industrial

General

Color	Black, White
Cord Range	0.325"-0.930"
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	5
Item Type	30A Grounding Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

Conductor Related

Cable Range	0.325 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
Nema Rating	L8-30P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	30
-----------------	----

Product Assets

- [Catalog Page - WDK B-42 Catalog Page](#)
- [Catalog Page - WDK B-37 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL2641 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1651_INSTALLINST](#)
- [Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_HBL2641_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock Devices](#)

Related Products

[HBL6031 - Weatherproofing Boots, Weatherproof Device](#)

	copper wire only.	Boot, Black
Type	<ul style="list-style-type: none"> Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 Plugs Plugs 	<p>HBLTL2CCBR - Twist-Lock Devices, Colored Cord Clamp, Size 2, Brown</p> <p>HBL2646 - Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30R, Screw Terminal, White</p> <p>HBLTL2CCBL - Twist-Lock Devices, Colored Cord Clamp, Size 2, Blue</p> <p>HBL2640 - Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30R, Screw Terminal, Black</p>
UPC	783585039008	

Dimensions

Dimensions	2.26 in x 2.26 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.26 in
Weight	0.3 lb
Width	2.26 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL2641-SPEC-EN | REV 1/2024