



Watertight Devices, Twist-Lock® Plug, 20A, 125/250V AC, 3 Pole, 3 Wire, Thermoplastic elastomer, NON-NEMA, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL26W08](#)



Watertight Twist-Lock® Plug, 20A, 125/250V AC, 3-Pole, 3 Wire, Thermoplastic elastomer, NON-NEMA.

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Item Type	20A Watertight Twist-Lock® Plug
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Rated for current interruption per UL498 • Electrical - Dielectric Voltage - 2500V AC • Electrical - Max Working Voltage - As marked • Electrical - Temperature Rise - 30°C max per UL498 at rated current • Environmental - UV resistance - All exposed materials are UV stabilized • Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P • Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous • Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)
Type	<ul style="list-style-type: none"> • Plugs • Plugs
UPC	783585456294

Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. Cord: 16/3 SJ, 18/3 S, 18/4 SJ, 18/4 S, 18/5 S;Max. Cord: 10/3 S, 10/4 S, 10/5 S

Certifications and Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK C-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL26W08 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2635_INSTALLINST](#)
- [Literature - Watertight Wiring Devices](#)
- [Sales Drawings - WDK_HBL26W_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Watertight Products](#)

Related Products

- [HBL67W08 - Watertight Devices, Twist-Lock® Receptacle with Lift Cover, 20A, 125/250VAC, 3 Pole, 3 Wire, Thermoplastic elastomer, NON-NEMA, Yellow](#)
- [HBLWTCS2 - Watertight Devices, Accessories, Cone Seal, 20A Twist-Lock, Black](#)
- [HBL 27W08 - Watertight Devices, Twist-Lock® Connector, 20A](#)

HBLWTB2 - Watertight Devices, Accessories, Bushing, 20A
Twist-Lock, Black
HBLWTB2 - Watertight Devices, Accessories, Bushing, 20A,
125/250V AC, 3 Pole, 3 Wire, Thermoplastic elastomer, NON-
NEMA, Yellow
HBLWTB2 - Watertight Devices, Accessories, Bushing, 20A
Twist-Lock, Black



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL26W08-SPEC-EN | REV 1/2024