



Watertight Devices, Twist-Lock® Plug, 20A, 125V AC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L5-20P, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL26W47](#)



Twist-Lock® Watertight Male Plug 20A, 125V, 2-Pole, 3-Wire, Thermoplastic Elastomer, NEMA L5-20P.

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Item Type	20A Watertight Twist-Lock® Plug
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Rated for current interruption per UL498 • Electrical - Dielectric Voltage - 2500V AC • Electrical - Max Working Voltage - As marked • Electrical - Temperature Rise - 30°C max per UL498 at rated current • Environmental - UV resistance - All exposed materials are UV stabilized • Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P • Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous • Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)
Type	<ul style="list-style-type: none"> • Plugs • Plugs
UPC	783585131382

Dimensions

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. Cord: 16/3 SJ, 18/3 S, 18/4 SJ, 18/4 S, 18/5 S;Max. Cord: 10/3 S, 10/4 S, 10/5 S

Certifications and Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L5-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK C-7 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL26W47 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2635_INSTALLINST](#)
[Literature - Food Processing Guide](#)
[Literature - Watertight Wiring Devices](#)
[Literature - Safety Product Guide](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_HBL26W47_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Watertight Products](#)

Related Products

[HBL67W47 - Watertight Devices, Twist-Lock® Receptacle with Lift Cover, 20A, 125VAC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L5-20R, Yellow.](#)
[HBL27W47 - Watertight Devices, Twist-Lock® Connector, 20A, 125V, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L5-20R, Yellow](#)
[HBLWTCS2 - Watertight Devices, Accessories, Cone Seal, 20A](#)

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

Twist-Lock, Black

HBLWTB2 - Watertight Devices, Accessories, Bushing, 20A
Twist-Lock, Black



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL26W47-SPEC-EN | REV 1/2024