

Locking Devices, Twist-Lock®, Safety Shroud, Angled Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, L14- 30R, Screw Terminal, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL2710AR](#)



Locking Devices, Twist-Lock®, Safety-Shroud®, Angled Receptacle, One Gang, 30A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA L14- 30R, Screw Terminal, Gray.

Features

- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use
- Engineered thermoplastic housing is impact and corrosion resistant, making it suitable for heavy-duty industrial environments

Application

Heavy Duty Industrial Shrouded

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2710AR
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2(2)
Item Type	30A Safety-Shroud® Receptacle
Material	Valox™
Material - Mounting Hardware	Screw Mounting

Number Of Poles
Number of Gang(s)
Operating Temperature

3-Pole
1-Gang
Maximum continuous 75°C and minimum -40°C without Impact

Specifications

- Body Contact Carrier - Natural (white) nylon
- Body Holding Screws - Steel, zinc plated
- Contacts - Brass
- Housing / Flange - Gray RPT
- Mounting Plate - Steel, zinc plated
- Terminal Retainer - Clear polycarbonate

Type
UPC

Receptacle
783585234649

Dimensions

Dimensions	4.77 in x 2.85 in x 3.14 in
Display Size	Standard Sized Product
Height	3.14 in
Length	4.77 in
Weight	0.9 lb
Width	2.85 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L14-30R

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalog Page - WDK B-31 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL2710AR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1291_INSTALLINST](#)
[Sales Drawings - WDK_HBL2710AR_DRAWING_PDF](#)
[Specifications - HBL2710AR Specification Sheet French](#)
[Specifications - Wiring HBL2710AR Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Twist-Lock Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL2710AR-SPEC-EN | REV 10/2024