

EdgeConnect™ Twist-Lock®,
Flanged Receptacle, 30A 125/250V,
Screwless Terminal, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2716ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial,
Flanged Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding,
L14-30R, Screwless Terminal, White

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

General

Catalog Number	HBL2716ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	3
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Flanged Receptacle
UPC	783585719184

Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	Withstands 3,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Industry Standard(s)	Listed to UL 498, Fed.Spec. W-C-596, Certified to CSA C22.2 No.42
Nema Rating	L14-30R

Logistics

Carton Quantity	40
-----------------	----

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - EdgeConnect Brochure](#)
- [Catalog Page - WDK B-31 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2974](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M14336](#)
- [Specifications - HBL2716ST Specification Sheet](#)
- [Specifications - Wiring HBL2716ST specification sheet](#)
- [Specifications - HBL2716ST Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)