

EdgeConnect™ Twist-Lock®,
Flanged Receptacle, 30A 3-Phase
Delta 480V AC, Screwless Terminal,
White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2736ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial,
Flanged Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire
Grounding, L16-30R, Screwless Terminal, White

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

General

Catalog Number	HBL2736ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	3
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Flanged Receptacle
UPC	783585719191

Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	Withstands 3,000V minimum
Phase	3-Phase
Voltage Rating	3P 480 VAC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Industry Standard(s)	Listed to UL 498, Fed.Spec. W- C-596, Certified to CSA C22.2 No.42
Nema Rating	L16-30R

Logistics

Carton Quantity	40
-----------------	----

Product Assets

[Brochures - EdgeConnect Brochure French](#)
[Brochures - EdgeConnect Brochure](#)
[Catalog Page - WDK B-33 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD2974](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - Entertainment Product Solution Guide](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M14336](#)
[Specifications - HBL2736ST Specification Sheet](#)
[Specifications - Wiring HBL2736ST specification sheet](#)
[Specifications - HBL2736ST Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)