

Locking Devices, Twist-Lock®,
Single Flush Receptacle, 30A, 4
Pole, 5 Wire Grounding, 240/415
VAC, 3 Phase Y, NEMA L26-30R,
Black Nylon

By Hubbell Wiring Device-Kellems
Catalog # [HBL2800](#)

Locking Devices, Twist-Lock®,Single Flush Receptacle, 30A, 4
Pole, 5 Wire Grounding, 240/415 VAC, 3 Phase Y, NEMA L26-
30R, Black Nylon

Features

- High-impact, abuse-resistant nylon face
- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion

Performance

- Electrical-Current Interrupting - Certified at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)
- Environmental - Moisture Resistance - IP20 Suitability

General

Catalog Number	HBL2800
EU RoHS Indicator	Contact Manufacturer
Item Type	30A Single Flush Receptacle
Listings	<ul style="list-style-type: none">• UL 498• Fed.Spec. W-C-596• CSA C22.2 No.42
Number Of Poles	4-Pole



UPC 783585580357

Dimensions

Height 1.23 in
Length 2.38 in

Conductor Related

Number Of Wires 5-Wire
Wire Size #16 AWG to #8 AWG

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK B-35 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL2800 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2445_INSTALLINST](#)
[Literature - Twist-Lock® Devices for Data Centers](#)
[Sales Drawings - WDK_HBL2800_DRAWING_PDF](#)
[Specifications - Wiring HBL2800 Specification Sheet](#)
[Specifications - HBL2800 Specification Sheet](#)
[Specifications - HBL2800 Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Twist-Lock Devices](#)