

EdgeConnect™ Twist-Lock®,
Female Connector Body, 30A 3-
Phase Wye 277/480V AC, Black and
White,

By Hubbell Wiring Device-Kellems
Catalog # [HBL2823ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Female
Connector Body, 30A 3-Phase Wye 277/480V AC, L22-30R,
Screwless Terminal, Black and White

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Superior cord grip design protects terminations from excess strain

General

Catalog Number	HBL2823ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	4
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Connector
UPC	783585719139

Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	Withstands 3,000V minimum
Phase	3-Phase
Voltage Rating	3PY 277/ 480 VAC

Conductor Related

Number Of Wires	5
-----------------	---

Certifications And Compliance

Industry Standard(s)	Listed to UL 498, Fed.Spec. W- C-596, Certified to CSA C22.2 No.42
Nema Rating	L22-30R

Logistics

Carton Quantity	30
-----------------	----

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - EdgeConnect Brochure](#)
- [Catalog Page - WDK B-35 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2973](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M14335](#)
- [Specifications - HBL2823ST Specification Sheet French](#)
- [Specifications - Wiring HBL2823ST specification sheet](#)
- [Specifications - HBL2823ST Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)