

Watertight Devices, Twist-Lock®
Plug, 30A, 3 Phase 600V AC, 3 Pole,
4 Wire, Thermoplastic elastomer,
NEMA L17-30P, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL28W77](#)

Watertight Devices, Twist-Lock® Plug, 30A, 3 Phase 600V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L17-30P, Yellow

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous
- Mechanical - Cord Accommodation - 0.375"-1.000" (9.5-25.4)

General

Catalog Number	HBL28W77
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	30A Watertight Twist-Lock® Plug
Number Of Poles	3-Pole
UPC	783585131740

Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in
Length	2.77 in
Width	2.77 in



Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min Cords: 12/3 SJ, 16/3 S, 14/4 SJ, 18/4 S, 18/5 S;Max Cord: 8/3 S, 8/4 S, 10/5 S

Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L17-30P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK C-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL28W77 AutoCAD Drawing](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Watertight Wiring Devices](#)
- [Sales Drawings - M-12627](#)
- [Specifications - Wiring HBL28W77 Specification Sheet](#)
- [Specifications - HBL28W77 Specification Sheet](#)
- [Specifications - HBL28W77 Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Hubbell Watertight Devices](#)
- [Video - Watertight Products](#)
- [Video - Watertight Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-HBL28W77-SPEC-EN | REV 4/2025