



Wiring Device-Kellems

Watertight Devices, Twist-Lock® Connector, 30A, 125/250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L14-30R, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL29W74](#)



Watertight Devices, Twist-Lock® Connector, 30A, 125/250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L14-30R.

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Item Type	30A Watertight Twist-Lock® Connector
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Rated for current interruption per UL498 • Electrical - Dielectric Voltage - 2500V AC • Electrical - Max Working Voltage - As marked • Electrical - Temperature Rise - 30°C max per UL498 at rated current • Environmental - UV resistance - All exposed materials are UV stabilized • Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P • Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous • Mechanical - Cord Accommodation - 0.375"-1.000" (9.5-25.4)

Type	<ul style="list-style-type: none"> • Connector Body • Connector Body
------	--

UPC 783585131870

Dimensions

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	Min Cords: 12/3 SJ, 16/3 S, 14/4 SJ, 18/4 S, 18/5 S;Max Cord: 8/3 S, 8/4 S, 10/5 S

Certifications and Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L14-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK C-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL29W74 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2635_INSTALLINST](#)
- [Literature - Food Processing Guide](#)
- [Literature - Watertight Wiring Devices](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_HBL29W74_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Watertight Products](#)

Related Products

[HBLWTCS3 - Watertight Devices, Accessories, Cone Seal, 30A Twist-Lock, Black](#)

[HBL28W74 - Watertight Devices, Twist-Lock® Plug, 30A, 125/250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L14-30P, Yellow](#)

[HBLWTB3 - Watertight Devices, Accessories, Bushing, 30A Twist-Lock, Black](#)

[HBL50W54 - Watertight Devices, Accessories, Closure Cap,](#)

Dimensions	2.77 in x 2.77 in x 5.67 in
Height	5.67 in
Length	2.77 in
Width	2.77 in



A proud member of the Hubbell Family.