

Extra Heavy Duty Industrial Grade,  
Pilot Light Toggle Switches, General  
Purpose AC, Double Pole, 30A  
120/277V AC, Back and Side Wired  
Toggle

By Hubbell Wiring Device-Kellems  
Catalog # [HBL3032PL](#)

Switches and Lighting Controls, Extra Heavy Duty Industrial  
Grade, Pilot Light Toggle Switches, General Purpose AC, Double  
Pole, 30A 120/277V AC, Back and Side Wired, Red Toggle

Features

- Large brass binding head screws with deep slots
- Abuse resistant nylon toggle
- Strip gauge for accurate wiring

Application

Back and Side Wired

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 30A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. Solid and stranded copper wire only

General

Catalog Number	HBL3032PL
Color	Red
EU RoHS Indicator	Yes
Indicator	Light On with Load On
Number Of Poles	Double Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Base Material - Thermoset, Green</li><li>• Contacts - Silver Alloy</li><li>• Ground Screw - Brass (Green)</li></ul>



Style	Terminal Screws - Brass
Type	Toggle Material - Nylon
UPC	Top Material - Thermoset
	Double Pole
	Toggle
	783585434605

Dimensions

Dimensions	4.06 in x 1.31 in x 1.86 in
Height	1.86 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalog Page - WDK D-4 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL3032PL AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1244\\_INSTALLINST](#)  
[Literature - Healthcare Product Solutions](#)

[Sales Drawings - WDK\\_HBL3032PL\\_DRAWING\\_PDF](#)  
[Specifications - Wiring HBL3032PL Specification Sheet](#)  
[Specifications - HBL3032PL Specification Sheet](#)  
[Specifications - HBL3032PL Specification Sheet French](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
WDK\_CA-HBL3032PL-SPEC-EN | REV 4/2025