

Wallplates and Boxes, Marine  
Products, 24-32V DC, Receptacle,  
For Trolling Motor, Yellow,  
Corrosion Resistant

By Hubbell Wiring Device-Kellems  
Catalog # [HBL328DCR](#)



Wallplates and Boxes, Marine Products, 24-32V DC, Receptacle,  
For Trolling Motor, Yellow, Corrosion Resistant

Application

Electric Fishing Reel Devices

General

Catalog Number	HBL328DCR
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Weather Resistant
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"><li>Product Type - Electric Fishing Reel Devices</li><li>Version - Yellow Locking Receptacle</li></ul>
UPC	783585353166

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	28V DC kV

Voltage Rating Description	28V DC kV
Wattage	840

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#10 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	840

Product Assets

- [Catalog Page - WDK AA-34 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Sales Drawings - WDK\\_HBL328DCR\\_DRAWING\\_PDF](#)
- [Specifications - HBL328DCR Specification Sheet](#)
- [Specifications - HBL328DCR Specification Sheet French](#)
- [Specifications - WIRING\\_HBL328DCR\\_spec](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Marine Electrical Products](#)
- [Video - Marine Electrical Products](#)