



# Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 3-Phase Delta 250V AC, Non-NEMA

By Hubbell Wiring Device-Kellems  
Catalog # [HBL3433GCB](#)



Twist-Lock® Industrial Female Connector Body, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal.

## Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance
- Superior cord grip design protects terminations from excess strain
- Clear, funnel shaped wire entry for ease of termination
- Integral dust shield protects wiring chamber from dust or contaminants

## Application

Heavy Duty Industrial

## General

Color	Black, White
Cord Range	0.350"-1.150" (9-29)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Grounding Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded</li> </ul>

## Dimensions

Dimensions	2.33 in x 2.33 in x 3.86 in
Display Size	Standard
Height	3.86 in
Length	2.33 in
Weight	0.40 lb
Width	2.33 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

## Conductor Related

Cable Range	0.350 - 1.150 in
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

- [Catalog Page - WDK B-48 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - WIRING\\_PD1732\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_HBL3433GCB\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

## Related Products

- [HBLTL3CCBR - Twist-Lock Devices, Colored Cord Clamp, Size 3, Brown](#)
- [HBLTL3CCBL - Twist-Lock Devices, Colored Cord Clamp, Size 3, Blue](#)
- [HBLTL3CCBK - Twist-Lock Devices, Colored Cord Clamp, Size 3, Black](#)

AWG - 18 AWG standard  
copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

HBLTL3CCBR - Twist-Lock Devices, Colored Cord Clamp, Size 3, Black  
HBLTL3CCRD - Twist-Lock Devices, Colored Cord Clamp, Size 3, Red  
HBLTL3CCGR - Twist-Lock Devices, Colored Cord Clamp, Size 3, Green

Temperature Rating      Maximum continu : 75° C ;  
Minimum continu : -40° C sans impact, -25° avec impact.

Type                      • Connector Body  
                                 • Connector Body

UPC                        783585039909



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL3433GCB-SPEC-EN | REV 1/2024