

Heavy Duty Products, IEC Pin and Sleeve Devices, Marine Grade, Female, Connector Body, 63A 230V, 2-Pole 3-Wire Grounding, Terminal Screws, Watertight

Par Hubbell Wiring Device-Kellems
No de catalogue [HBL363CRC](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Marine Grade, Female, Connector Body, 63A 230V, 2-Pole 3-Wire Grounding, Terminal Screws, Blue, Watertight.



Performance

Environmental - Moisture Resistance - IP55 Suitability

Général

Numéro de catalogue	HBL363CRC
Couleur	
Indicateur RoHS de l'UE	Non
Conditions environnementales	Résistant aux intempéries
Isolation	Corps isolé
Type d'article	Version marine
Matériau	Composite
Matériau - Matériel de montage	Monté sur cordon
Nombre de pôles	2 pôles
Température nominale	Maximum continu : 75° C ; Minimum continu : -40° C sans impact, -25° avec impact.
CUP	783585454900

Dimensions

Taille de l'affichage	Standard
-----------------------	----------

Caractéristiques électriques

Intensité nominale	63 A
Connectivité	Bornes à vis
Courant / Intensité nominale	63 A
Valeur nominale actuelle	63 A
Tension Rating	230V kV

Chef d'orchestre

Gamme de conducteurs	Fil de cuivre #8 AWG à #2 AWG uniquement
Nombre de conducteurs	Mise à la terre à 3 fils

Certifications et conformité

Norme(s) industrielle(s)	Certifié CE
Nema Rating	Non-NEMA
Normes - Conformité à la directive RoHS	CM

Logistique

Quantité de cartons	5
---------------------	---

Documentation

- [Catalogues - WDK Catalog Full 2024](#)
- [Dessin technique - HBL363CRC AutoCAD Drawing](#)
- [Dessins de vente - WDK_HBL363CRC_DRAWING_PDF](#)
- [Garantie - Industrial & Commercial Products](#)
- [Littérature - Hubbell Marine Full Line Catalog](#)
- [Manuels d'installation - WIRING_HBL363CRC_INSTALLINST](#)
- [Page du catalogue - WDK AA-25 Catalog Page](#)
- [Spécifications - WIRING_HBL363CRC_spec](#)
- [Spécifications - HBL363CRC](#)
- [Vidéo - Marine Electrical Products](#)

