



4-PLEX Surge Suppression Receptacle, 2- Pole 3-Wire, 15A 125V, 5-15R, Blue

By Hubbell Wiring Device-Kellems
Catalog # [HBL415S](#)



4-PLEX Surge Suppression Receptacle, 2-Pole 3-Wire, 15A 125V, 5-15R.

Features

- Surge suppression with lights, 80 joules/6500A per mode
- Anchor hole and loop feature secures solid wire for fast, easy terminations
- Triple wipe contacts
- Easily accessible break-off tabs for split wiring
- Three conductors energize all four outlets

Application

4-Plex with LED

General

Color	<ul style="list-style-type: none"> • Blue • Bleu
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.50
Indicator(s) Type	LED Only
Item Type	Surge Protection Receptacles
Material	Polycarbonate
Material - Mounting Hardware	Mounting Screws
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Capable of withstanding a fault level of 1000A, per UL498 • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-12

Dimensions

Dimensions	4.30 in x 0.92 in x 4.30 in
Display Size	Standard
Height	4.30 in
Length	4.30 in
Weight	0.35 lb
Width	0.92 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Listed to UL Standard 498 File E2186 • NEMA® WD-6 Compliant
----------------------	--

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK A-32 Catalog Page](#)
- [Catalog Page - WDK M-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL415S AutoCAD Drawing](#)
- [Installation Manuals - WIRING_B04578H02_INSTALLINST Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBL415_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Accommodation - #14-12
AWG stranded or solid
copper conductor only

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498 and CSA

Response Time
Series
UPC

5
4-Outlet Receptacle
783585017853



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL415S-SPEC-EN | REV 1/2024