

Cord and Cable Reels, Industrial Series, 12/3 SJEO Cable, 45' Length, No Devices, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBL45123](#)

Cord and Cable Reels, Industrial Series, 12/3 SJEO Cable, 45' Length, No Devices, Yellow

Features

- Multi-position guide arm
- Positive-latch mechanism maintains desired cord length
- 12 AWG cord for greater current carrying capacity
- Plug-in 5 ft. long power cord requires no electrical wiring

Application

Bench, Ceiling and Wall Mounted

Performance

Environment - Operations - Dry, indoor, non-hazardous locations

General

Cable Length	45 Ft
Cable Type	#12/3 SJ
Catalog Number	HBL45123
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	No
Item Type	Reel with Stripped Leads
Series	Heavy Duty Industrial
Specifications	<ul style="list-style-type: none"><li>• Cable Feet (m) - 45 (13.7)</li><li>• Cable Type - 12/3 SJEO</li><li>• NEMA Style - 5-15R</li><li>• Weight Lbs. (kg) - 21 (9.5)</li></ul>
Type	Standard Reel With Leads
UPC	783585454580

Dimensions



Cable Length Active	540
Reel Frame Dimension	Steel

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Cable Specification	12/3 SJO
Nema Color	Yellow and Black

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA C22.2 No. 21 Certified</li><li>• UL 355 Listed</li></ul>
----------------------	--

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL45123 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1295\\_INSTALLINST](#)
- [Literature - GFCI Protected Double Duplex Receptacle Cord Reel](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Stainless Steel Cord Reels](#)
- [Sales Drawings - WDK\\_HBL45123\\_DRAWING\\_PDF](#)
- [Specifications - HBL45123 Specification Sheet French](#)
- [Specifications - HBL45123 Specification Sheet](#)
- [Specifications - WIRING\\_HBL45123\\_spec](#)
- [Warranty - Industrial & Commercial Products](#)