

HUBBELL Wiring Device-Kellems

By Hubbell Wiring Device-Kellems

Catalog # [HBL45123R20](#)

Cord and Cable Reels, Industrial Cord Reel, With Box and 5352GRY, 45' 12/3, Yellow.



Features

- Multi-position guide arm
- Positive-latch mechanism maintains desired cord length
- 12 AWG cord for greater current carrying capacity
- Plug-in 5 ft. long power cord requires no electrical wiring

General

Application	Bench, Ceiling and Wall Mounted
Base Type	Optional
Cable Length	45 Ft
Cable Type	#12/6 SJ
Catalog Number	HBL45123R20
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	Yes
Item Type	Reel with Portable Outlet Box and 1 Duplex Plate
Performance	Environment - Operations - Dry, indoor, non-hazardous locations
Series	Industrial
Type	Reel With Portable Outlet Box An 1-20A 125V Duplex Receptacle
UPC	783585451282

Dimensions

Cable Length Active	540
Cable Length Inactive	60
Reel Frame Dimension	Steel

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Cable Specification	12/3 SJEO
Feeder Cord	12/3 SJEO
Nema Color	Yellow and Black

Certifications And Compliance

Industry Standard(s)	CSA C22.2 No. 21 Certified UL 355 Listed
----------------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL45123R20 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1295_INSTALLINST](#)
- [Literature - Stainless Steel Cord Reels](#)
- [Literature - GFCI Protected Double Duplex Receptacle Cord Reel](#)
- [Literature - Food Processing Guide](#)
- [Literature - Industrial Solutions](#)
- [Literature - Safety Product Guide](#)
- [Sales Drawings - WDK_HBL45123R20_DRAWING_PDF](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL45123R20-SPEC-EN | REV 6/2024