

Cord and Cable Ree

By Hubbell Wiring Device-Kellems
Catalog # [HBL45123R220W](#)

Cord and Cable Reels, Industrial Series, 12/3 SJEO Cable, 45'
Length, With 2) Duplex Receptacles, Yellow



Features

- Multi-position guide arm
- Positive-latch mechanism maintains desired cord length
- 12 AWG cord for greater current carrying capacity
- Plug-in 5 ft. long power cord requires no electrical wiring

Application

Bench, Ceiling and Wall Mounted

Performance

Environment - Operations - Dry, indoor, non-hazardous locations

General

Cable Length	45 Ft
Cable Type	#12/6 SJ
Catalog Number	HBL45123R220W
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	Yes
Item Type	Reel with Portable Box and 2) 5252GRY Receptacles
Series	Industrial
Specifications	• Cable Feet (m) - 45 (13.7) • Cable Type - 12/3 SJEO • NEMA Style - 5-20R • Weight Lbs. (kg) - 29 (13.2)
Type	Reel With Portable Outlet Box And Two 20A Duplex Receptacles, White Housing

UPC783585198392

Dimensions

Cable Length Active	540
Reel Frame Dimension	Steel

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Cable Specification	12/3 SJO
Nema Color	Yellow and Black

Certifications And Compliance

Industry Standard(s)	• CSA C22.2 No. 21 Certified • UL 355 Listed
----------------------	--

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_HBL45123R220W_INSTALLINST](#)
[Literature - GFCI Protected Double Duplex Receptacle Cord Reel](#)
[Literature - Stainless Steel Cord Reels](#)
[Sales Drawings - WDK_HBL45123R220W_DRAWING_PDF](#)
[Specifications - HBL45123R220W Specification Sheet French](#)
[Specifications - HBL45123R220W Specification Sheet English](#)

