

EdgeConnect™ Twist-Lock®  
Locking Devices, Single Receptacle,  
15A 250V, 2-Pole 3-Wire Grounding

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4560ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Single Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screwless Terminal, Black

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Application

Industrial

General

Catalog Number	HBL4560ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	2
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Receptacle
UPC	783585719658

Electrical Ratings

Current / Amperage Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC



Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Listed to UL 498</li><li>• Fed.Spec. W-C-596</li><li>• Certified to CSA C22.2 No.42</li></ul>
Nema Rating	L6-15R

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - EdgeConnect Brochure](#)
- [Catalog Page - WDK B-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14595\\_ACAD](#)
- [Installation Manuals - PD3024](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M14595](#)
- [Specifications - HBL4560ST Specification Sheet](#)
- [Specifications - Wiring HBL4560ST specification sheet](#)
- [Specifications - HBL4560ST Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)