

EdgeConnect™ Twist-Lock®  
Locking Devices, Panel Mount  
Receptacle, 15A 250V, 2-Pole 3-  
Wire Grounding

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4563ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Panel Mount Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screwless Terminal, 1.75" or 1.937" Mounting, Black

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Application

Industrial

General

|                          |                                                        |
|--------------------------|--------------------------------------------------------|
| Catalog Number           | HBL4563ST                                              |
| Environmental Conditions | IP20 Suitability                                       |
| Material                 | Nylon                                                  |
| Mounting Type            | Screw Mount                                            |
| Number Of Poles          | 2                                                      |
| Series                   | EdgeConnect™                                           |
| Size                     | Standard Sized Product                                 |
| Style                    | Locking Devices                                        |
| Temperature Rating       | Maximum Continuous 75°C,<br>Minimum -40°C (w/o impact) |
| Type                     | Receptacle                                             |
| UPC                      | 783585719641                                           |

Electrical Ratings

|                           |                           |
|---------------------------|---------------------------|
| Current / Amperage Rating | 15 A                      |
| Dielectric Strength       | Withstands 2,000V minimum |
| Phase                     | Single Phase              |
| Voltage Rating            | 250 VAC                   |

Conductor Related

|                 |   |
|-----------------|---|
| Number Of Wires | 3 |
|-----------------|---|

Certifications And Compliance

|                      |                                                                                                                                       |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• Listed to UL 498</li><li>• Fed.Spec. W-C-596</li><li>• Certified to CSA C22.2 No.42</li></ul> |
| Nema Rating          | L6-15R                                                                                                                                |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Brochures - EdgeConnect Brochure French](#)  
[Brochures - EdgeConnect Brochure](#)  
[Catalog Page - WDK B-13 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M14595\\_ACAD](#)  
[Installation Manuals - PD3024](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Literature - EdgeConnect™ Technology](#)  
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)  
[Sales Drawings - M14595](#)  
[Specifications - Wiring HBL4563ST specification sheet](#)  
[Specifications - HBL4563ST Specification Sheet](#)  
[Specifications - HBL4563ST Specification Sheet French](#)  
[Warranty - Industrial & Commercial Products](#)