



# Locking Devices, Twist-Lock®, VariLoad, Male Plug, 20A 3-Phase Wye 120/208V AC- 400Hz, Non-NEMA, Screw Terminal, Unique Center Pin

By Hubbell Wiring Device-Kellems  
Catalog # [HBL45915](#)



Locking Devices, Twist-Lock®, VariLoad®, Male Plug, 20A 3-Phase Wye 120/208V AC only - 400Hz, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black Non Metallic Body, Unique Center Pin.

## Features

- Heat resistant thermoset construction
- Non-interchangeable center pin configuration to be designated to different circuits

## Application

Heavy Duty Industrial

## General

Color	Black
Cord Range	0.625"-1.00"
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A VariLoad® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstand 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL 94 or CSA 22.2 No. 0.6</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #14 AWG - #10 AWG stranded copper wire only.</li> <li>• Mechanical - Terminal Identification - Terminals identified in accordance</li> </ul>

## Dimensions

Dimensions	2.13 in x 2.13 in x 3.79 in
Display Size	Standard Sized
Height	3.79 in
Length	2.13 in
Weight	0.4 lb
Width	2.13 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3 Phase WYE 120/208 VAC

## Conductor Related

Cable Range	0.625 - 1.00 in
Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	Listed to UL 498
----------------------	------------------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK B-49 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Installation Manuals - WIRING\\_PD1189\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_HBL45915\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

## Related Products

[HBL45905 - Locking Devices, Twist-Lock®, VariLoad, Flush Receptacle, 20A 3-Phase Wye 120/208V AC- 400Hz, Non-](#)

Type	Identified in accordance with UL 498	NEMA, Screw Terminal, Unique Center Pin
	<ul style="list-style-type: none"><li>Plugs</li><li>Plugs</li></ul>	HBL45935 - Locking Devices, Twist-Lock®, VariLoad, Female Connector Body, 20A 3-Phase Wye 120/208V AC- 400Hz, Non-NEMA, Screw Terminal, Unique Center Pin
UPC	783585238104	HBL6027 - Weatherproofing Boots, Weatherproof Device Boot, Black



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL45915-SPEC-EN | REV 1/2024