

EdgeConnect™ Twist-Lock®  
Locking Devices, Panel Mount  
Receptacle, 15A 125V, 2-Pole 3-Wire  
Grounding

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4713ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Panel Mount Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screwless Terminal, 1.75" or 1.937" Mounting, Black

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Application

Industrial

General

Catalog Number	HBL4713ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	2
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Receptacle
UPC	783585719665

Electrical Ratings

Current / Amperage Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Listed to UL 498</li><li>• Fed.Spec. W-C-596</li><li>• Certified to CSA C22.2 No.42</li></ul>
Nema Rating	L5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - EdgeConnect Brochure French](#)  
[Brochures - EdgeConnect Brochure](#)  
[Catalog Page - WDK B-13 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M14595\\_ACAD](#)  
[Installation Manuals - PD3024](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Literature - EdgeConnect™ Technology](#)  
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)  
[Sales Drawings - M14595](#)  
[Specifications - HBL4713ST Specification Sheet](#)  
[Specifications - HBL4713ST Specification Sheet French](#)  
[Specifications - Wiring HBL4713ST specification sheet](#)  
[Warranty - Industrial & Commercial Products](#)