

EdgeConnect™ Twist-Lock®
Locking Devices, Flush Receptacle,
15A 277V AC, 2-Pole 3-Wire
Grounding

By Hubbell Wiring Device-Kellems
Catalog # [HBL4760ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Flush
Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R,
Screwless Terminal, Black

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Application

Industrial

General

Catalog Number	HBL4760ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	2
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Receptacle
UPC	783585719610

Electrical Ratings

Current / Amperage Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	277 VAC



Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Listed to UL 498• Fed.Spec. W-C-596• Certified to CSA C22.2 No.42
Nema Rating	L7-15R

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Brochures - EdgeConnect Brochure French](#)
[Brochures - EdgeConnect Brochure](#)
[Catalog Page - WDK B-13 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - M14595_ACAD](#)
[Installation Manuals - PD3024](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M14595](#)
[Specifications - HBL4760ST Specification Sheet French](#)
[Specifications - HBL4760ST Specification Sheet](#)
[Specifications - Wiring HBL4760ST specification sheet](#)
[Warranty - Industrial & Commercial Products](#)