

Replaced by HBL4P50ALU, Surge Arrestors, 40KA, 120/208V AC Three Phase Y, Type 1

By Hubbell Wiring Device-Kellems
Catalog # [HBL4SA40](#)



Surge Arrestors, 40KA, 120/208V AC ThreePhase Y, Type 1

Features

- Surge arrestors are a low cost solution that may be installed on the line side or load side of the service entrance
- Excellent for OEM applications where size is an important variable
- Single phase wired-in surge protective devices feature a compact design

General

Catalog Number	HBL4SA40
EU RoHS Indicator	Contact Manufacturer
Series	Wired-In Surge Devices
Type	40kA
UPC	783585833118

Electrical Ratings

Voltage Rating	Wye 120/208 VAC
Voltage Rating Description	120/208 VAC Wye

Product Assets

- [Catalog Page - WDK M-22 Catalog Page](#)
- [Catalog Page - WDK M-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL4SA40 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_HBL_SA40 INSTALLATION INSTRUCTIONS_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBL4SA40_DRAWING_PDF](#)
- [Specifications - WIRING_HBL4SA40_spec](#)
- [Specifications - HBL4SA40 Specification Sheet English](#)
- [Specifications - HBL4SA40 Specification Sheet French](#)
- [Warranty - SPD Series: 36kA, 40kA & 80kA](#)