

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 5-15P, Extra Large Cord

By Hubbell Wiring Device-Kellems
Catalog # [HBL5266EBK](#)

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15P, Black, Single Pack, Extra Large Cord

Features

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 HB or better, Environmental - IP Suitability - IP20, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-15P
Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • Fed. Spec. W-C596G • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A
Voltage Rating	125 VAC



Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Length	1.52 in
Weight	0.15 lb.
Height	1.96 in
Width	1.52 in
Dimensions	1.52 in x 1.52 in x 1.96 in

General

Color	Black
Style	Standard
Series	Insulgrip®
Specifications	• Assembly Screws - Nickel plated steel • Blade Holder - Nylon • Blades - .060 in. (1.5) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
UPC	783585366111
Type	Plug
Item Type	Insulgrip Plug
Material	Polycarbonate

Logistics

Pallet Quantity	3600
Carton Quantity	10

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.50

Product Assets

- Catalog [English]
- Catalog Page [English]
- Installation Manual [French]
- Installation Manual [Spanish]



A Hubbell brand