

Insulgrip® Series, Straight Blade Devices,
Female Connector Body, Insulgrip Heavy
Duty, Industrial/Commercial Grade, Straight,
15A 125V, 5-15R and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5269C](#)

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty,
Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A
125V, 5-15R, Black and White, Single Pack

Features

- Receptacle only - does not include reel
- Single Outlet

Application

Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full
rated current, Electrical - Dielectric Voltage - Withstands 2,000V
minimum, Environmental - Flammability - UL 94 HB or better,
Environmental - IP Suitability - IP20, Environmental - Operating
Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact),
Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper
wire only, Mechanical - Terminal Identification - Terminals identified in
accordance with UL 498 and CSA

Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R
Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole
Conductor Range	#18 AWG to #10 AWG

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A
Voltage Rating	125 VAC



Connectivity	Screw Terminals
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Length	2.65 in
Display Size	Standard
Weight	0.15 lb.
Height	2.65 in
Width	1.55 in
Dimensions	2.65 in x 1.55 in x 2.65 in

General

Color	Black, White
Style	Standard
Cord Range	0.300"-0.660" (7.6-16.8)
Specifications	• Assembly Screws - Nickel plated steel • Contact Holder - Nylon • Contacts - .040 in. (1.0) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
UPC	783585173252
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	Insulgrip Plug
Material	Polycarbonate

Logistics

Pallet Quantity	3600
Carton Quantity	10

Operational

Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
--------------------	--

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.50

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French\]](#)
- [Installation Manual \[Spanish\]](#)



A Hubbell brand