

Straight Blade Connector Body, Insulgrip HeavyDuty, Industrial/Commercial, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Blue and White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5269CBL](#)

Straight Blade Devices, Female Connector Body, Insulgrip HeavyDuty, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Blue and White, Single Pack

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 HB or better, Environmental - IP Suitability - IP20, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R
Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole
Conductor Range	#14 AWG to #12 AWG

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum



Current Rating	15 A
Voltage Rating	125 V
Connectivity	Screw Terminals
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Display Size	Standard
Weight	0.2 lb.

General

Color	Blue, White
Style	Standard
Cord Range	0.300"-0.660" (7.6-16.8)
Series	Insulgrip
Specifications	• Assembly Screws - Nickel plated steel • Contact Holder - Nylon • Contacts - .040 in. (1.0) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
UPC	783585173313
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	Insulgrip Plug
Material	Polycarbonate

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with
--------------------	--

Operating Temperature

impact.
Maximum continuous 75°C and
minimum -40°C without Impact

Product Assets

- Catalog [English]
- Catalog Page [English]
- Installation Manual [French]



A Hubbell brand