

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 30A 3-Phase Wye 120/208V AC, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL530R9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding , Terminal Screws, Blue, Watertight

Features

- Corrosion-resistant self-closing gasketed cover
- Insulated non-metallic housing
- Color coded housings for easy identification

Application

High Ampacity Watertight Connections

Performance


Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - 3000V AC, Electrical - Max. Working Voltage - 600V RMS, Electrical - Temperature Rise - Max. 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%, Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17, Environmental - Ingress Protection - IP67 Suitability, Environmental - Moisture Resistance - Watertight per IEC 60309-1, Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum - 40°C w/o impact, Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682, Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing, Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

Specifications

Environmental Conditions	Watertight
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA
Industry Standard(s)	• CSA StandardC22.2 No. 182.1 • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146032

Conductor

Number Of Wires	5-Wire
Wire Size	#12 AWG to #8 AWG
Number Of Poles	4-Pole



Current

Amperage Rating	30 A
Voltage Rating Description	3 Phase Y 120/208 VAC
Current Rating	30 A
Voltage Rating	3 Phase Y 120/208 VAC
Wattage	6240
Connectivity	Pressure Terminal Screws
Phase	Three Phase
Current / Amperage Rating	30 A

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Color	Blue
Style	Standard Service
Series	HBL Heavy Duty
Specifications	• Cover - Reinforced Thermoplastic Polyester • Cover Screw - Nickel-plated brass • Gaskets - Solid Neoprene • Housing - Zytel® 101 Nylon • Mounting Flange - Zytel® 101 Nylon
UPC	783585405520
Type	Watertight Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Single Flanged
Material	Thermoplastic

Logistics

Pallet Quantity	250
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)