



Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5352](#)



HBL® Extra Heavy Duty MAX Compact Duplex Straight Blade Receptacle 20A, 2-Pole, 3-Wire Grounding, 125V 5-20R.

Features

- Slender/compact design
- Brass Mounting Strap
- Triple wipe contacts

Application

Extra Heavy Duty Compact

General

Color	<ul style="list-style-type: none"> • Brown • Marron
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only • Mechanical - Terminal

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.2 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C596G • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-11 Catalog Page](#)
[Catalog Page - WDK O-33 Catalog Page](#)

	Identification - Terminals identified in accordance with UL 498 and CSA	Catalogs - WDK Catalog Full 2023 Engineering Drawing - HBL5352 AutoCAD Drawing Installation Manuals - WIRING_PD2615_INSTALLINST Literature - Wiring Device Solutions for Strategic Manufacturing Facilities Literature - Entertainment Product Solution Guide Sales Drawings - WDK_HBL5352_DRAWINGS_PDF Warranty - Industrial & Commercial Products
Series	Heavy Duty	
Style	Finder Groove Face	
Type	<ul style="list-style-type: none">• Standard Duplex• Standard Duplex	
UPC	783585434964	



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5352-SPEC-EN | REV 1/2024