



Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Yellow, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5364VY](#)



Valise® Straight Blade Male Plug 20A, 2-Pole, 3-Wire Grounding, 125V, 5-20P Nylon.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

Application

Industrial/Commercial Grade

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Horsepower - Maximum	1
Item Type	Valise
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical:Current Interrupting: Certified for current interrupting at full rated current • Dielectric Voltage: Withstands 2,000V minimum • Mechanical :Terminal Accommodation #18-#12 AWG stranded copper wire only • Terminal Identification: Terminals identified in accordance with UL 498 and CSA • Environmental :Flammability: UL 94 HB or better • IP Suitability: IP20

Dimensions

Dimensions	1.87 in x 1.25 in x 1.87 in
Height	1.87 in
Length	1.87 in
Weight	0.1 lb
Width	1.25 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No 42 File 280C • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
----------------------	---

Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-37 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1237_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)

- Operating Temperatures:
Maximum continuous 75°C
- minimum -40°C (w/o
impact)

Series	Valise®
Style	Standard
Type	<ul style="list-style-type: none">• Plug• Plugs
UPC	783585013169



A proud member of the Hubbell Family.