



Wiring Device-Kellems

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 5-20R and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL5369C](#)

Insulgrip® Straight Female Connector 20A, 2-Pole, 3-Wire Grounding, 20A 125V, 5-20R/White.

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial Grade

General

Color	<ul style="list-style-type: none"> • Noir, blanc • Noir, blanc
Cord Range	0.250"-0.655" (6.4-16.6)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Insulgrip Plug
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 HB or better • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)

Dimensions

Dimensions	2.78 in x 1.41 in x 1.53 in
Display Size	Standard
Height	1.53 in
Length	2.78 in
Weight	0.15 lb
Width	1.41 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
----------------------	---

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK A-38 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL5369C AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2437_INSTALLINST](#)

	<ul style="list-style-type: none"> • Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Insulgrip®
Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none"> • Connector Body • Connector Body
UPC	783585174259

[Installation Manuals - WIRING_PDI214_INSTALLINST](#)
[Literature - Food Processing Guide](#)
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
[Literature - Industrial Solutions](#)
[Literature - Education Application Guide](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_HBL5369C_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5369C-SPEC-EN | REV 1/2024