

Straight Blade Devices, Female Connector,
Insulgrip Heavy Duty,
Industrial/Commercial Grade, Straight, 20A
125V, 5-20R, Rated for 12/3 SO

By Hubbell Wiring Device-Kellems
Catalog # [HBL5369EBK](#)

Straight Blade Devices, Female Connector, Insulgrip Heavy Duty,
Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding,
20A 125V, 5-20R, Black, Single Pack, Rated for 12/3 SO

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 HB or better, Environmental - IP Suitability - IP20, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-20R
Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole
Conductor Range	#18 AWG to #10 AWG

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum



Current Rating	20 A
Voltage Rating	125 VAC
Connectivity	Screw Terminals
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Weight	0.15 lb.
--------	----------

General

Color	Black
Style	Standard
Cord Range	0.250"-0.655" (6.4-16.6)
Series	Insulgrip®
Specifications	• Assembly Screws - Nickel plated steel • Contact Holder - Nylon • Contacts - .040 in. (1.0) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
UPC	783585541396
Type	Connector Body
Item Type	Insulgrip Plug

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	1.00

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[French\]](#)



A Hubbell brand