

Temporary Power Products, Spider
Portable Power, Replacement Parts,
Flush Receptacle, 50A 125/250V, 3-
Pole 4-Wire Grounding

By Hubbell Wiring Device-Kellems
Catalog # [HBL53R61](#)

Temporary Power Products, Spider Portable Power,
Replacement Parts, Flush Receptacle, 50A 125/250V, 3-Pole 4-
Wire Grounding

Features

- Spider Portable Power
- Replacement Parts
- Flush Receptacle
- 50A 125/250V

Application

Heavy Duty Industrial

General

Catalog Number	HBL53R61
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Code Compliance - NEC®, ANSI/NFPA 70• Enclosure Type - 3R, rainproof, suitable for use in damp locations• Environment - Moisture Resistance
Style	Receptacle
Type	Replacement Part
UPC	783585369617

Dimensions

Display Size	Standard Sized Product
--------------	------------------------



Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	2500

Conductor Related

Wire Size	#14 AWG to #12 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL 1640 cUL and CSA, UL 943
----------------------	-----------------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK H-13 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_HBL53R61_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL53R61_DRAWING_PDF](#)
[Specifications - HBL53R61 Specification Sheet](#)
[Specifications - HBL53R61 Specification Sheet French](#)
[Specifications - Wiring HBL53R61 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)