

Heavy Duty Products, IEC Pin and Sleeve  
Devices, Industrial Grade, Female,  
Mechanically Interlocked Receptacle, 60A 3-  
Phase Wye 120/208V AC

By Hubbell Wiring Device-Kellems  
Catalog # [HBL560MI9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial  
Grade, Female, Mechanically Interlocked Receptacle, 60A 3-  
Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Terminal  
Screws

Features

- Large gears enclosed in a gear box
- Lockable handle to meet OSHA Lockout/Tagout regulations
- Pre-wired IEC Pin and Sleeve receptacle

Application

High Ampacity Watertight Connections

Performance

Electrical - Current Interrupting - Certified for current  
interrupting at full rated current and voltage, Electrical -  
Dielectric Voltage - Withstands 3,000V AC Min, Electrical - Max.  
Working Voltage - 600V AC RMS, Environmental - Flammability -  
UL94-5VA and V-O Classification, Environmental - Ingress  
Protection - IP67 Suitability, Environmental - Moisture Resistance  
- Outdoor - 4X (Watertight, Washdown), Indoor - 12 (Dust-tight,  
Falling Dirt and Noncorrosive Liquids)., Environmental -  
Operating Temperature - Max. Continuous +75°C, Min.  
Continuous -40°C, Mechanical - Impact Resistance - In  
accordance with UL 746C, Mechanical - Mounting - External  
adjustable feet, Mechanical - Product Identification -  
Identification and ratings are part of the external label and  
molded into the receptacle mount, Mechanical - Terminal  
Identification - In accordance with UL, CSA and international  
conventions

Specifications

|                          |            |
|--------------------------|------------|
| Environmental Conditions | Watertight |
| EU RoHS Indicator        | No         |
| Nema Rating              | Non-NEMA   |
| Industry Standard(s)     | UL Listed  |

Conductor

|                 |                  |
|-----------------|------------------|
| Number Of Wires | 5-Wire           |
| Wire Size       | #8 AWG to #2 AWG |
| Number Of Poles | 4-Pole           |



Current

|                            |                          |
|----------------------------|--------------------------|
| Amperage Rating            | 60 A                     |
| Voltage Rating Description | 3 Phase Y 120/208 VAC    |
| Current Rating             | 60 A                     |
| Voltage Rating             | 3 Phase Y 120/208 VAC    |
| Wattage                    | 12480                    |
| Connectivity               | Pressure Terminal Screws |
| Phase                      | Three Phase              |
| Current / Amperage Rating  | 60 A                     |

Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

General

|                              |                                                                                                                                                                                            |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Color                        | Blue                                                                                                                                                                                       |
| Style                        | Standard Service                                                                                                                                                                           |
| Series                       | Non-Fused                                                                                                                                                                                  |
| Specifications               | <ul style="list-style-type: none"><li>• Base - Valox®</li><li>• Conduit Hub - Zinc</li><li>• Enclosure Gasket - Neoprene</li><li>• Face - Valox®</li><li>• Shaft Seal - Neoprene</li></ul> |
| UPC                          | 783585406176                                                                                                                                                                               |
| Type                         | Mechanical Interlock                                                                                                                                                                       |
| Material - Mounting Hardware | Screw Mounting                                                                                                                                                                             |
| Item Type                    | Mechanically Interlocked Single                                                                                                                                                            |
| Material                     | Thermoplastic                                                                                                                                                                              |

Logistics

|                 |    |
|-----------------|----|
| Pallet Quantity | 84 |
| Carton Quantity | 1  |

Product Assets

- [Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[English\]](#)