

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 15A 250V, 6-15R and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5669C](#)

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 250V, 6-15R, Black and White, Single Pack

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 HB or better, Environmental - IP Suitability - IP20, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #18-10 AWG copper conductors only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	6-15R
Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706

Conductor

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole
Conductor Range	#14 AWG to #12 AWG

Current



Amperage Rating	15 A
Voltage Rating Description	250 V
Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A
Voltage Rating	250 V
Wattage	3750 W
Connectivity	Screw Terminals
Current / Amperage Rating	15 A

Dimensions

Length	2.78 in
Display Size	Standard
Weight	0.15 lb.
Height	1.53 in
Width	1.53 in
Dimensions	2.78 in x 1.53 in x 1.53 in

General

Type	Standard
Cord Range	0.230"-0.720" (5.8-18.3)
Series	Insulgrip®
Specifications	• Assembly Screws - Nickel plated steel • Contact Holder - Nylon • Contacts - .040 in. (1.0) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
UPC	783585175805
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	Insulgrip
Material	Nylon

Logistics

Pallet Quantity	4000
-----------------	------

Carton Quantity	10	Product Assets
Operational		Catalog [English]
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact	Catalog Page [English]
Operating Temperature	Maximum continuous 75°C and minimum -40°C without impact	Installation Manual [French]

