



# Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Black, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5965VBLK](#)



Valise® Straight Blade Male Plug 15A, 2-Pole, 3-Wire  
Grounding, 125V, 1-15P.

## Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

## Application

Industrial/Commercial Grade

## General

Color	<ul style="list-style-type: none"> <li>• Noir</li> <li>• Noir</li> </ul>
Horsepower - Maximum	2
Item Type	Valise
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 HB or better</li> <li>• Environmental - IP Suitability - IP20</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire only</li> <li>• Mechanical - Terminal</li> </ul>

## Dimensions

Dimensions	1.87 in x 1.12 in x 1.87 in
Height	1.87 in
Length	1.87 in
Weight	0.1 lb
Width	1.12 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to C22.2 No 42 File 280C</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File E1706</li> </ul>
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-37 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Installation Manuals - WIRING\\_PD1237\\_INSTALLINST Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_HBL5965V\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

Identification - Terminals  
identified in accordance  
with UL 498 and CSA

Series	Valise®
Style	Standard
Type	<ul style="list-style-type: none"><li>• Plug</li><li>• Plugs</li></ul>
UPC	783585013084



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL5965VBLK-SPEC-EN | REV 1/2024