



Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R



By Hubbell Wiring Device-Kellems
Catalog # [HBL5969VBLK](#)

Valise® Straight Blade Female Connector Body 15A, 2-Pole, 3-Wire Grounding, 125V, 1-15R.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

Application

Industrial/Commercial

General

Color	<ul style="list-style-type: none"> • Black • Noir
Cord Range	0.220"-.660" (5.6-16.8)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.50
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 HB or better • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Terminal

Dimensions

Dimensions	2.68 in x 1.32 in x 2.68 in
Display Size	Standard
Height	2.68 in
Length	2.68 in
Weight	0.15 lb
Width	1.32 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280C • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-38 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1237_INSTALLINST Literature - WIRING_WLFVM034](#)

Accommodation - #18-12
AWG. Standed copper wire
only

Literature - Pulp & Paper Solutions
Sales Drawings - WDK_HBL5969V_DRAWING_PDF
Warranty - Industrial & Commercial Products

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498 and CSA

Series	Valise®
Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none">• Connector Body• Connector Body
UPC	783585013275



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5969VBLK-SPEC-EN | REV 1/2024