

Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM22](#)

Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, Yellow

Features

- New quick connect with backwards compatibility

Application

Straight Adapter

Performance

Environmental - Moisture Resistance - IP55 Suitability

General

Catalog Number	HBL61CM22
EU RoHS Indicator	No
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 15A 125V Straight Blade
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Receptacle Type	Female- 30A 125V Twist-Lock®
Specifications	• Adapter Style - Straight (Pig Tail) • Female End Rating - 30A 125V, 2P3W Twist-Lock® • Male End Rating - 15 or 20A 125V, 2P3W Straight Blade



UPC	• Poles and Wires - 2 Pole, 3 Wire Grounding • Product Type - Adapters 783585808598
-----	---

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	125 VAC
Wattage	3750

Logistics

Carton Quantity	6
Pallet Quantity	252

Product Assets

- [Catalog Page - WDK AA-28 Catalog Page](#)
- [Catalog Page - WDK AA-29 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2030_INSTALLINST](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Specifications - HBL61CM22 Specification Sheet English](#)
- [Specifications - HBL61CM22 Specification Sheet French](#)
- [Specifications - HBL61CM22](#)
- [Warranty - Industrial & Commercial Products](#)