



Wiring Device-Kellems

Adapter, Marine, Molded, Straight Blade, Yellow, 30A 125V 2-Pole 3-Wire Grounding Female to 50A 125V, 2-Pole 3- Wire Grounding Locking Male, Yellow

By Hubbell Wiring Device-Kellems
Catalog Number [HBL61CM56](#)



Adapter, Marine, Molded, Straight Blade, 30A 125V 2-Pole 3-Wire Grounding Female to 50A 125V, 2-Pole 3-Wire Grounding Locking Male.

Application

Straight Adapter

General

Color	Yellow
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 30A 125V Twist-Lock®
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability
Receptacle Type	Female- 50A 125V Twist-Lock®
UPC	783585808635

Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Voltage Rating	125 VAC
Wattage	6250

Product Assets

- [Catalog Page - Wiring_Catalog_BB29_CatPage](#)
- [Installation Manuals - WIRING_PD2030_INSTALLINST](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.