

Temporary Power Products, Spider
Portable Power, Replacement Parts,
Flanged Inlet, 50A 125/250V

By Hubbell Wiring Device-Kellems
Catalog # [HBL6375S](#)

Temporary Power Products, Spider Portable Power,
Replacement Parts, Flanged Inlet, 50A 125/250V

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

General

Catalog Number	HBL6375S
Color	Black
EU RoHS Indicator	No
Item Type	Flanged Single Male
Material	Steel, Zinc Plated
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	• Blades - Brass • Casing - Steel, zinc plated • Terminal Retainer - Phenolic • Terminal Screws - Steel
Style	Inlet
UPC	783585369594

Dimensions

Dimensions	3.80 in x 3.43 in x 3.75 in
Display Size	Standard Sized Product
Height	3.75 in
Length	3.8 in
Weight	0.8 lb
Width	3.43 in



Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Wire Size	#10 AWG to #6 AWG
-----------	-------------------

Certifications And Compliance

Industry Standard(s)	• Certified to CSA C22.2 No.42 • Listed to UL 498
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Pallet Quantity	996

Product Assets

[Catalog Page - WDK B-57](#) [Catalog Page - WDK H-13](#) [Catalog Page - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_HBL6375S_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL6375S_DRAWING_PDF](#)
[Specifications - HBL6375S Specification Sheet French](#)
[Specifications - HBL6375S Specification Sheet](#)
[Specifications - Wiring HBL6375S Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Twist-Lock Devices](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-HBL6375S-SPEC-EN | REV 4/2025