

Watertight Devices, Twist-Lock®
Receptacle with Lift Cover, 30A, 3
Phase 250V AC, 3 Pole, 4 Wire,
Thermoplastic elastomer, NEMA
L15-30R, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL69W75BK](#)

Watertight Devices, Twist-Lock® Receptacle with Lift Cover,
30A, 3 Phase 250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer,
NEMA L15-30R, Black

Features

- Impact resistant PBT lid, cover plate, and receptacle body
- Thermoplastic elastomer seal
- Stainless steel hardware and corrosion-resistant connection points

Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous

General

Catalog Number	HBL69W75BK
EU RoHS Indicator	Contact Manufacturer
Item Type	30A Watertight Twist-Lock® Receptacle
Number Of Poles	3-Pole
Type	Receptacle
UPC	783585511320

Dimensions

Dimensions	4.56 in x 3.10 in x 2.92 in
Height	2.92 in



Length	4.56 in
Width	3.1 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	• IP69K In Use • Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L15-30R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK C-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Specifications - Wiring HBL69W75BK Specification Sheet](#)
- [Specifications - HBL69W75BK Specification Sheet](#)
- [Specifications - HBL69W75BK Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Watertight Products](#)
- [Video - Watertight Products](#)