

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL6PS350A](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A
125V, 6 Outlet, 350 Joules, 6' Cord, Office White.

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.
- Cordon de 6 pieds
- Garantie de 5 000\$ pour panne de lignes
- Volets inviolables

General

Application	
Catalog Number	HBL6PS350A
Color	Office White Blanc cassé
EU RoHS Indicator	Yes
Environmental Conditions	
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	6
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	Electrical - Max Surge Current - 6.5kA Electrical - Max. Operating Voltage - 130 Electrical - Operating Frequency - 50/60Hz Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
Series	Economy Surge Strips
Type	
UPC	783585120515

Dimensions

Display Size	350 Joules
--------------	------------

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	1
Pallet Quantity	480

Product Assets

[Catalog Page - WDK M-9 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL6PS350A AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2380_INSTALLINST](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_HBL6PS350_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL6PS350A-SPEC-EN | REV 6/2024