



# Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 4-Pole 4-Wire Non- Grounding, 60A 3 Phase 120/208 V AC, 18-60R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7303C](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 4-Pole 4-Wire Non-Grounding, 60A 3 Phase 120/208 V AC, 18-60R, Black, Single Pack.

## Features

- Catalog number, ratings and certifications molded in face
- Gripping ribs provide secure gripping area
- Supertough nylon housing

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Cord Range	0.625"-1.310"
Horsepower - Maximum	7.5
Material	Nylon
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 HB</li> <li>• Environmental - IP Suitability - IP20</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only</li> <li>• Mechanical - Terminal Identification - Terminals</li> </ul>

## Dimensions

Dimensions	4.13 in x 2.88 in x 2.88 in
Height	2.88 in
Length	4.13 in
Weight	0.85 lb
Width	2.88 in

## Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed File E1706</li> </ul>
Nema Rating	18-60P

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

- [Catalog Page - WDK A-49 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL7303C AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1191\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL7303C\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

identified in accordance  
with UL 498 and CSA

Series	Extra Heavy Duty
Style	Non-Grounding
Type	<ul style="list-style-type: none"><li>• Plug</li><li>• Plugs</li></ul>
UPC	783585015385



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL7303C-SPEC-EN | REV 1/2024