

HUBBELL
Wiring Device-Kellems

**Locking Devices, Midget Twist-Lock®,
Industrial, Male Plug, 15A 125V AC, 2-Pole
3-Wire Grounding, NEMA ML-2P**

By Hubbell Wiring Device-Kellems
Catalog # [HBL7594](#)

Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A
125V AC, 2-Pole 3-Wire Grounding, NEMA ML-2P, Screw Terminal,
Black nylon cover, phenolic body, multiple drive screw terminals



Features

- Abuse resistant nylon housing
- Phenolic body for high heat resistance
- Angled body design for low profile in tight spaces
- Totally insulated body adds extra measure of safety

Application

Industrial/Commercial

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17, Environmental - Moisture Resistance - IP20 Suitability, Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact), Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper wire only., Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Nema Rating	ML-2P
Industry Standard(s)	• Certified to CSA C22.2 No.42 • Listed to UL 498

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG
Number Of Poles	2-Pole
Cable Range	0.300 - 0.430 in

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum



A Hubbell brand

Current Rating	15 A
Voltage Rating	125 V
Connectivity	Pressure Terminal Screws
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Length	1.17 in
Display Size	Midget Locking
Weight	0.10 lb.
Height	2.45 in
Width	1.17 in
Dimensions	1.17 in x 1.17 in x 2.45 in

General

Color	Black
Cord Range	0.281"-0.421"(7.1-10.7)
Specifications	• Blade Holder - Phenolic • Blades - Brass • Housing - Nylon • Terminal Clamp - Zinc plated steel with black lacquer finish • Terminal Screws - #5-40 Brass
UPC	783585237770
Type	Plugs
Material - Mounting Hardware	Cord Mounted
Item Type	15A Midget Twist-Lock® Plug
Material	Nylon

Logistics

Pallet Quantity	12000
Carton Quantity	10

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

Catalog [English]
Catalog Page [English]
Installation Manual [English]