



Straight Blade Devices, Male Plug, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15P, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8013V](#)



Straight Blade Male Plug, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15P.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors

Application

Hospital Grade

General

Color	<ul style="list-style-type: none"> • White • Blanc
Cord Range	0.300"-0.360" (7.6-9.1)
Horsepower - Maximum	0.5
Item Type	Valise Plug
Material	Nylon
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2000V AC minimum • Environmental - Flammability - UL 94 HB • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #18 to #16 AWG • Mechanical - Terminal Identification - Terminals identified in accordance
-------------	--

Dimensions

Dimensions	1.6 in x 1.24 in x 1.17 in
Height	1.17 in
Length	1.6 in
Weight	0.1 lb
Width	1.24 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #16 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK L-11 Catalog Page](#)
[Catalog Page - WDK A-36 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1459_INSTALLINST Literature - Duct Products Guide](#)
[Sales Drawings - WDK_HBL8013V_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

with UL 498 and CSA

Series	Hospital Grade
Style	<ul style="list-style-type: none">• Valise• Insulation Displacement
Type	<ul style="list-style-type: none">• Plugs• Plugs
UPC	783585016177



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL8013V-SPEC-EN | REV 1/2024