



Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15R, Red, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8200HRED](#)



HBL® Extra Heavy Duty MAX Compact Hospital Grade Duplex Receptacle 15A, 2-Pole, 3-Wire Grounding, 125V, 5-15R, Red.

Features

- Slender/compact design
- Finder Groove Face
- Triple wipe contacts

Application

Hospital Grade

General

Color	<ul style="list-style-type: none"> • Rouge • Rouge
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.25 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	--

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-9](#) [Catalog Page - WDK L-4](#) [Catalog Page - WDK L-4](#)

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Catalogs - [WDK Catalog Full 2023](#)
Engineering Drawing - [HBL8200HRED AutoCAD Drawing](#)
Installation Manuals - [WIRING_PD2615_INSTALLINST](#)
Literature - [Duct Products Guide](#)
Sales Drawings - [WDK_HBL8200H_DRAWINGS_PDF](#)
Warranty - [Industrial & Commercial Products](#)

Series Hospital Grade
Style Thermoplastic Polyester Face
Type

- Receptacle
- Receptacle

UPC 783585247502



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL8200HRED-SPEC-EN | REV 1/2024