



# Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Red, Illuminated Face

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8200ILR](#)



HBL® Extra Heavy Duty MAX Hospital Grade Duplex Flush LED Illuminated Receptacle 15A, 125V, 5-15R, Red.

## Features

- Slender/compact design
- Impact-resistant finder groove face
- Triple wipe contacts
- Entire face illuminated by two LEDs

## Application

Extra Heavy Duty Hospital Grade

## General

Color	<ul style="list-style-type: none"> <li>• Red</li> <li>• Rouge</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Polycarbonate
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 V-0</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid</li> </ul>

## Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.2 lb
Width	1.33 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified, C22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
----------------------	--

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-9](#) [Catalog Page](#)  
[Catalog Page - WDK L-4](#) [Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Installation Manuals - WIRING\\_PD2615\\_INSTALLINST](#)

AWG standard or solid  
copper wire only

- Mechanical - Terminal  
Identification - Terminals  
identified in accordance  
with UL 498 and CSA

[Literature - Duct Products Guide](#)  
[Literature - Healthcare Application Guide](#)  
[Sales Drawings - WDK\\_HBL8200IL\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

Series Hospital Grade  
Style Finder Groove Face  
Type

- Receptacle
- Receptacle

UPC 783585016467



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL8200ILR-SPEC-EN | REV 1/2024