



# Straight Blade Devices, Receptacles, Duplex, Tamper Resistant Hospital Grade, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8200SGGYA](#)



Straight Blade Duplex Receptacle, Tamper Resistant Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R.

## Features

- Unique tamper-resistant contact mechanism prevents injury
- Integral wire leads for fast installation and no exposed live parts
- One-piece nickel-plated brass ground strap
- I.D. marking surface helps in quick circuit identification

## Application

Extra Heavy Duty Hospital Grade

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94V-0 and UL 94-5 VA</li> <li>• Environmental - IP Suitability - IP20</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Ground Terminal Accommodation - #12-#10 AWG stranded or</li> </ul>

## Dimensions

Dimensions	3.29 in x 1.65 in x 1.27 in
Display Size	Standard Sized Product
Height	1.27 in
Length	3.29 in
Weight	0.35 lb
Width	1.65 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Wire Leads
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified, C22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-9 Catalog Page](#)  
[Catalog Page - WDK L-4 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Installation Manuals - WIRING\\_PD1763\\_INSTALLINST](#)  
[Literature - Duct Products Guide](#)

- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

[Literature - Education Application Guide](#)  
[Sales Drawings - WDK\\_HBL8200SG\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Tamper-Resistant Receptacles](#)

Series  
Style  
Type  
  
UPC

Hospital Grade  
Tamper Resistant  

- Receptacle
- Receptacle

  
783585152240



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL8200SGGYA-SPEC-EN | REV 1/2024