



Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Angled, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Transparent, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8215CAT](#)



Insulgrip® Straight Blade Hospital Grade Angle Male Plug 15A, 2-Pole, 3-Wire Grounding, 125V, 5-15P, Transparent.

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Transparent for easy visual inspection of termination

Application

Hospital Grade

General

Color	<ul style="list-style-type: none"> • Transparent • Transparent
Cord Range	0.250"-0.655" (6.4-16.6)
Horsepower - Maximum	0.5
Item Type	Insulgrip Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2000V AC minimum • Environmental - Flammability - UL 94 HB or better • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #18-10 AWG • Mechanical - Terminal Identification - Terminals

Dimensions

Height	2.11 in
Thickness	1.22
Weight	0.15 lb
Width	1.53 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • UL Listed to UL498 File E1706
----------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------

Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-11 Catalog Page](#)
- [Catalog Page - WDK A-36 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - WIRING_PD1215_INSTALLINST](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Duct Products Guide](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - Healthcare Application Guide](#)
- [Sales Drawings - WDK_HBL8215CAT_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

Identification - terminals
identified in accordance
with UL 498 and CSA

Series	Hospital Grade
Style	Insulgrip
Type	<ul style="list-style-type: none">• Plug• Plug
UPC	783585179254



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL8215CAT-SPEC-EN | REV 1/2024